

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581417

Luminaire Tested: **HC407D010-HM40525827-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525827-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 726.4 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581417

CATALOG NUMBER: HC407D010-HM40525827-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581417

CATALOG NUMBER: HC407D010-HM40525827-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63819
5°	63345
10°	61697
15°	60069
20°	57388
25°	53459
30°	47072
35°	37132
40°	26954
45°	19816
50°	16119
55°	13505
60°	12236
65°	11266
70°	10459
75°	9531
80°	8666
85°	7359



TEST NUMBER: P581417

CATALOG NUMBER: HC407D010-HM40525827-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	6.6
10°-20°	132.0	18.2
20°-30°	178.9	24.6
30°-40°	153.5	21.1
40°-50°	90.7	12.5
50°-60°	57.4	7.9
60°-70°	38.6	5.3
70°-80°	21.3	2.9
80°-90°	6.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.1	49.4
0°-40°	512.5	70.6
0°-60°	660.6	90.9
0°-90°	726.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	726.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	512	48
15°	470	132
25°	393	179
35°	247	153
45°	114	91
55°	63	57
65°	39	39
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P581417

CATALOG NUMBER: HC407D010-HM40525827-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	517.4
2.5°	513.7
5°	511.6
7.5°	504.8
10°	492.6
12.5°	482.1
15°	470.4
17.5°	455.7
20°	437.2
22.5°	416.6
25°	392.8
27.5°	364.8
30°	330.5
32.5°	289.8
35°	246.6
37.5°	204.8
40°	167.4
42.5°	136.2
45°	113.6
47.5°	97.2
50°	84.0
52.5°	72.8
55°	62.8
57.5°	55.0
60°	49.6
62.5°	44.4
65°	38.6
67.5°	33.8
70°	29.0
72.5°	24.2
75°	20.0
77.5°	15.8
80°	12.2
82.5°	8.4
85°	5.2
87.5°	2.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)