

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593170

Luminaire Tested: **HC625D010-HM60525850-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC625D010-HM60525850-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2642.0 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593170

CATALOG NUMBER: HC625D010-HM60525850-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P593170

CATALOG NUMBER: HC625D010-HM60525850-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 111 | 108 | 104 | 101 | 109 | 105 | 102 | 100 | 101 | 99 | 96 | 97 | 95 | 94 | 94 | 92 | 91 | 89 | | | 89 |
| 2 | 104 | 97 | 92 | 87 | 101 | 95 | 90 | 86 | 92 | 88 | 84 | 89 | 85 | 83 | 86 | 83 | 81 | 79 | | | 79 |
| 3 | 97 | 88 | 82 | 77 | 94 | 87 | 81 | 76 | 84 | 79 | 75 | 81 | 77 | 73 | 79 | 75 | 72 | 70 | | | 70 |
| 4 | 90 | 81 | 73 | 68 | 88 | 79 | 73 | 68 | 77 | 71 | 67 | 75 | 70 | 66 | 73 | 69 | 65 | 63 | | | 63 |
| 5 | 84 | 74 | 67 | 61 | 83 | 73 | 66 | 61 | 71 | 65 | 60 | 69 | 64 | 60 | 67 | 63 | 59 | 57 | | | 57 |
| 6 | 79 | 68 | 61 | 55 | 77 | 67 | 60 | 55 | 66 | 59 | 55 | 64 | 59 | 54 | 63 | 58 | 54 | 52 | | | 52 |
| 7 | 74 | 63 | 56 | 50 | 73 | 62 | 55 | 50 | 61 | 55 | 50 | 60 | 54 | 50 | 58 | 53 | 49 | 48 | | | 48 |
| 8 | 70 | 59 | 51 | 46 | 69 | 58 | 51 | 46 | 57 | 50 | 46 | 56 | 50 | 46 | 54 | 49 | 46 | 44 | | | 44 |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 47 | 43 | 53 | 47 | 42 | 52 | 46 | 42 | 51 | 46 | 42 | 41 | | | 41 |
| 10 | 63 | 51 | 44 | 40 | 61 | 51 | 44 | 40 | 50 | 44 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 38 | | | 38 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 100074 |
| 5° | 99604 |
| 10° | 97399 |
| 15° | 95114 |
| 20° | 91539 |
| 25° | 86570 |
| 30° | 78677 |
| 35° | 63677 |
| 40° | 42945 |
| 45° | 29515 |
| 50° | 24187 |
| 55° | 21161 |
| 60° | 20020 |
| 65° | 18887 |
| 70° | 17727 |
| 75° | 16860 |
| 80° | 15311 |
| 85° | 13398 |



TEST NUMBER: P593170

CATALOG NUMBER: HC625D010-HM60525850-61NDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 170.9 | 6.5 |
| 10°-20° | 470.6 | 17.8 |
| 20°-30° | 653.9 | 24.7 |
| 30°-40° | 582.2 | 22.0 |
| 40°-50° | 309.1 | 11.7 |
| 50°-60° | 202.1 | 7.7 |
| 60°-70° | 144.8 | 5.5 |
| 70°-80° | 83.9 | 3.2 |
| 80°-90° | 24.5 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1295.4 | 49.0 |
| 0°-40° | 1877.5 | 71.1 |
| 0°-60° | 2388.7 | 90.4 |
| 0°-90° | 2642.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2642.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1826 | |
| 5° | 1810 | 171 |
| 15° | 1676 | 471 |
| 25° | 1431 | 654 |
| 35° | 952 | 582 |
| 45° | 381 | 309 |
| 55° | 221 | 202 |
| 65° | 146 | 145 |
| 75° | 80 | 84 |
| 85° | 21 | 25 |
| 90° | 0 | |



TEST NUMBER: P593170

CATALOG NUMBER: HC625D010-HM60525850-61NDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1825.5 |
| 2.5° | 1815.7 |
| 5° | 1810.0 |
| 7.5° | 1788.5 |
| 10° | 1749.7 |
| 12.5° | 1714.7 |
| 15° | 1675.9 |
| 17.5° | 1627.4 |
| 20° | 1569.1 |
| 22.5° | 1503.1 |
| 25° | 1431.2 |
| 27.5° | 1347.7 |
| 30° | 1242.9 |
| 32.5° | 1116.7 |
| 35° | 951.5 |
| 37.5° | 769.0 |
| 40° | 600.1 |
| 42.5° | 466.1 |
| 45° | 380.7 |
| 47.5° | 324.3 |
| 50° | 283.6 |
| 52.5° | 250.5 |
| 55° | 221.4 |
| 57.5° | 200.0 |
| 60° | 182.6 |
| 62.5° | 165.0 |
| 65° | 145.6 |
| 67.5° | 128.2 |
| 70° | 110.6 |
| 72.5° | 95.1 |
| 75° | 79.6 |
| 77.5° | 64.0 |
| 80° | 48.5 |
| 82.5° | 35.0 |
| 85° | 21.3 |
| 87.5° | 9.6 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)