

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581448

Luminaire Tested: **HC4R07D010-HM40525835-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P581448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R07D010-HM40525835-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 919.3 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581448

CATALOG NUMBER: HC4R07D010-HM40525835-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P581448

CATALOG NUMBER: HC4R07D010-HM40525835-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74		
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60		
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56		
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52		
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104178
5°	106408
10°	110619
15°	110662
20°	102305
25°	88409
30°	71926
35°	52822
40°	30545
45°	14269
50°	6601
55°	2301
60°	740
65°	525
70°	397
75°	286
80°	0
85°	0



TEST NUMBER: P581448

CATALOG NUMBER: HC4R07D010-HM40525835-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	9.0
10°-20°	240.2	26.1
20°-30°	295.8	32.2
30°-40°	215.9	23.5
40°-50°	70.4	7.7
50°-60°	11.7	1.3
60°-70°	1.8	0.2
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.8	67.3
0°-40°	834.7	90.8
0°-60°	916.9	99.7
0°-90°	919.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	919.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	845	
5°	859	83
15°	867	240
25°	650	296
35°	351	216
45°	82	70
55°	11	12
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581448

CATALOG NUMBER: HC4R07D010-HM40525835-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	844.6
2.5°	845.2
5°	859.4
7.5°	876.0
10°	883.2
12.5°	880.8
15°	866.6
17.5°	831.0
20°	779.4
22.5°	717.2
25°	649.6
27.5°	579.1
30°	505.0
32.5°	429.1
35°	350.8
37.5°	272.1
40°	189.7
42.5°	123.9
45°	81.8
47.5°	53.9
50°	34.4
52.5°	20.1
55°	10.7
57.5°	4.1
60°	3.0
62.5°	2.4
65°	1.8
67.5°	1.1
70°	1.1
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)