

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582076

Luminaire Tested: **HC625D010-HM60525930-61NDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582076  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525930-61NDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2330.6 lumens  
Efficiency: N/A  
Efficacy: 87.0 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582076

CATALOG NUMBER: HC625D010-HM60525930-61NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582076

CATALOG NUMBER: HC625D010-HM60525930-61NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	139188
5°	139461
10°	141759
15°	142793
20°	130532
25°	102568
30°	75081
35°	53257
40°	25190
45°	9606
50°	4307
55°	1176
60°	504
65°	389
70°	240
75°	318
80°	0
85°	0



TEST NUMBER: P582076

CATALOG NUMBER: HC625D010-HM60525930-61NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.4	10.4
10°-20°	695.4	29.8
20°-30°	773.5	33.2
30°-40°	483.2	20.7
40°-50°	114.8	4.9
50°-60°	16.4	0.7
60°-70°	3.4	0.1
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1711.4	73.4
0°-40°	2194.6	94.2
0°-60°	2325.8	99.8
0°-90°	2330.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2330.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2539	
5°	2534	242
15°	2516	695
25°	1696	774
35°	796	483
45°	124	115
55°	12	16
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P582076

CATALOG NUMBER: HC625D010-HM60525930-61NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2539.0
2.5°	2528.2
5°	2534.3
7.5°	2543.6
10°	2546.6
12.5°	2545.1
15°	2516.0
17.5°	2418.0
20°	2237.5
22.5°	1983.4
25°	1695.7
27.5°	1420.3
30°	1186.1
32.5°	991.7
35°	795.8
37.5°	584.6
40°	352.0
42.5°	203.5
45°	123.9
47.5°	79.6
50°	50.5
52.5°	29.1
55°	12.3
57.5°	6.1
60°	4.6
62.5°	4.6
65°	3.0
67.5°	3.0
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)