

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582079

Luminaire Tested: **HC625D010-HM60525930-61PSMDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582079  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525930-61PSMDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2166.9 lumens  
Efficiency: N/A  
Efficacy: 80.9 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582079

CATALOG NUMBER: HC625D010-HM60525930-61PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582079

CATALOG NUMBER: HC625D010-HM60525930-61PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	77450
5°	77240
10°	76090
15°	74881
20°	72415
25°	68980
30°	62978
35°	50708
40°	34171
45°	24917
50°	21543
55°	19459
60°	18463
65°	17473
70°	16429
75°	15547
80°	14490
85°	13460



TEST NUMBER: P582079

CATALOG NUMBER: HC625D010-HM60525930-61PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.8	6.1
10°-20°	370.5	17.1
20°-30°	520.6	24.0
30°-40°	463.4	21.4
40°-50°	259.0	12.0
50°-60°	184.5	8.5
60°-70°	134.2	6.2
70°-80°	77.6	3.6
80°-90°	24.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.9	47.3
0°-40°	1487.3	68.6
0°-60°	1930.8	89.1
0°-90°	2166.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2166.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1413	
5°	1404	133
15°	1319	371
25°	1140	521
35°	758	463
45°	321	259
55°	204	185
65°	135	134
75°	73	78
85°	21	24
90°	0	



TEST NUMBER: P582079

CATALOG NUMBER: HC625D010-HM60525930-61PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1412.8
2.5°	1406.6
5°	1403.6
7.5°	1391.3
10°	1366.9
12.5°	1343.8
15°	1319.4
17.5°	1285.7
20°	1241.3
22.5°	1192.4
25°	1140.4
27.5°	1076.1
30°	994.9
32.5°	890.9
35°	757.7
37.5°	607.7
40°	477.5
42.5°	381.2
45°	321.4
47.5°	281.7
50°	252.6
52.5°	226.5
55°	203.6
57.5°	185.2
60°	168.4
62.5°	153.1
65°	134.7
67.5°	119.4
70°	102.5
72.5°	87.2
75°	73.4
77.5°	59.6
80°	45.9
82.5°	33.7
85°	21.4
87.5°	10.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)