

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582101

Luminaire Tested: **HC625D010-HM60525935-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582101  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525935-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2598.6 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582101

CATALOG NUMBER: HC625D010-HM60525935-61WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582101

CATALOG NUMBER: HC625D010-HM60525935-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45	45	45	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92120
5°	93363
10°	96859
15°	105341
20°	117774
25°	123963
30°	109131
35°	75697
40°	45199
45°	21491
50°	8111
55°	3393
60°	1053
65°	830
70°	529
75°	339
80°	505
85°	0



TEST NUMBER: P582101

CATALOG NUMBER: HC625D010-HM60525935-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.3	6.3
10°-20°	533.0	20.5
20°-30°	913.3	35.1
30°-40°	709.3	27.3
40°-50°	234.5	9.0
50°-60°	36.0	1.4
60°-70°	6.4	0.2
70°-80°	2.4	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1609.5	61.9
0°-40°	2318.8	89.2
0°-60°	2589.2	99.6
0°-90°	2598.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2598.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1680	
5°	1697	163
15°	1856	533
25°	2049	913
35°	1131	709
45°	277	234
55°	36	36
65°	6	6
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P582101

CATALOG NUMBER: HC625D010-HM60525935-61WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1680.4
2.5°	1678.9
5°	1696.6
7.5°	1715.9
10°	1740.0
12.5°	1788.4
15°	1856.1
17.5°	1938.3
20°	2018.8
22.5°	2065.6
25°	2049.4
27.5°	1938.3
30°	1724.0
32.5°	1435.6
35°	1131.1
37.5°	858.8
40°	631.6
42.5°	446.3
45°	277.2
47.5°	154.6
50°	95.1
52.5°	58.0
55°	35.5
57.5°	17.7
60°	9.6
62.5°	8.0
65°	6.4
67.5°	4.9
70°	3.3
72.5°	3.3
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)