

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582096

Luminaire Tested: **HC625D010-HM60525935-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582096  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525935-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2192.5 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582096

CATALOG NUMBER: HC625D010-HM60525935-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582096

CATALOG NUMBER: HC625D010-HM60525935-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	83047
5°	82654
10°	80827
15°	78928
20°	75962
25°	71841
30°	65282
35°	52842
40°	35631
45°	24491
50°	20068
55°	17557
60°	16611
65°	15683
70°	14714
75°	13979
80°	12723
85°	11133



TEST NUMBER: P582096

CATALOG NUMBER: HC625D010-HM60525935-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.8	6.5
10°-20°	390.6	17.8
20°-30°	542.6	24.7
30°-40°	483.1	22.0
40°-50°	256.5	11.7
50°-60°	167.7	7.6
60°-70°	120.2	5.5
70°-80°	69.6	3.2
80°-90°	20.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.0	49.0
0°-40°	1558.1	71.1
0°-60°	1982.2	90.4
0°-90°	2192.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2192.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1515	
5°	1502	142
15°	1391	391
25°	1188	543
35°	790	483
45°	316	256
55°	184	168
65°	121	120
75°	66	70
85°	18	20
90°	0	



TEST NUMBER: P582096

CATALOG NUMBER: HC625D010-HM60525935-61NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1514.9
2.5°	1506.9
5°	1502.0
7.5°	1484.2
10°	1452.0
12.5°	1423.0
15°	1390.7
17.5°	1350.5
20°	1302.1
22.5°	1247.4
25°	1187.7
27.5°	1118.4
30°	1031.3
32.5°	926.6
35°	789.6
37.5°	638.2
40°	497.9
42.5°	386.8
45°	315.9
47.5°	269.1
50°	235.3
52.5°	207.9
55°	183.7
57.5°	166.0
60°	151.5
62.5°	137.0
65°	120.9
67.5°	106.4
70°	91.8
72.5°	78.9
75°	66.0
77.5°	53.1
80°	40.3
82.5°	29.1
85°	17.7
87.5°	8.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)