

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581506

Luminaire Tested: **HC407D010-HM40525930-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525930-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 725.6 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581506

CATALOG NUMBER: HC407D010-HM40525930-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581506

CATALOG NUMBER: HC407D010-HM40525930-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89	89	89	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79	79	79	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70	70	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63	63	63	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57	57	57	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52	52	52	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47	47	47	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44	44	44	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40	40	40	40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37	37	37	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61525
5°	61190
10°	60082
15°	58804
20°	56298
25°	52343
30°	46346
35°	36560
40°	27357
45°	21037
50°	17078
55°	14172
60°	12532
65°	11587
70°	10711
75°	9817
80°	8879
85°	7076



TEST NUMBER: P581506

CATALOG NUMBER: HC407D010-HM40525930-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	6.4
10°-20°	129.2	17.8
20°-30°	175.4	24.2
30°-40°	151.9	20.9
40°-50°	95.4	13.1
50°-60°	60.0	8.3
60°-70°	39.4	5.4
70°-80°	21.7	3.0
80°-90°	5.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.3	48.4
0°-40°	503.2	69.3
0°-60°	658.5	90.8
0°-90°	725.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	499	
5°	494	47
15°	460	129
25°	385	175
35°	243	152
45°	121	95
55°	66	60
65°	40	39
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P581506

CATALOG NUMBER: HC407D010-HM40525930-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	498.8
2.5°	495.7
5°	494.2
7.5°	489.2
10°	479.7
12.5°	470.1
15°	460.5
17.5°	447.5
20°	428.9
22.5°	407.7
25°	384.6
27.5°	358.0
30°	325.4
32.5°	285.6
35°	242.8
37.5°	203.6
40°	169.9
42.5°	143.3
45°	120.6
47.5°	103.6
50°	89.0
52.5°	76.5
55°	65.9
57.5°	56.8
60°	50.8
62.5°	45.3
65°	39.7
67.5°	34.1
70°	29.7
72.5°	24.6
75°	20.6
77.5°	16.0
80°	12.5
82.5°	8.5
85°	5.0
87.5°	2.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)