

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582132

Luminaire Tested: **HC630D010-HM63040827-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC630D010-HM63040827-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2786.2 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582132

CATALOG NUMBER: HC630D010-HM63040827-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582132

CATALOG NUMBER: HC630D010-HM63040827-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105529
5°	105035
10°	102715
15°	100301
20°	96533
25°	91294
30°	82962
35°	67157
40°	45285
45°	31120
50°	25500
55°	22317
60°	21106
65°	19924
70°	18721
75°	17771
80°	16164
85°	14152



TEST NUMBER: P582132

CATALOG NUMBER: HC630D010-HM63040827-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.2	6.5
10°-20°	496.3	17.8
20°-30°	689.5	24.7
30°-40°	614.0	22.0
40°-50°	325.9	11.7
50°-60°	213.1	7.6
60°-70°	152.8	5.5
70°-80°	88.6	3.2
80°-90°	25.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1366.0	49.0
0°-40°	1980.0	71.1
0°-60°	2519.0	90.4
0°-90°	2786.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2786.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1925	
5°	1909	180
15°	1767	496
25°	1509	690
35°	1004	614
45°	401	326
55°	234	213
65°	154	153
75°	84	89
85°	22	26
90°	0	



TEST NUMBER: P582132

CATALOG NUMBER: HC630D010-HM63040827-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1925.0
2.5°	1914.8
5°	1908.7
7.5°	1886.1
10°	1845.2
12.5°	1808.4
15°	1767.3
17.5°	1716.2
20°	1654.7
22.5°	1585.1
25°	1509.3
27.5°	1421.2
30°	1310.6
32.5°	1177.6
35°	1003.5
37.5°	811.0
40°	632.8
42.5°	491.5
45°	401.4
47.5°	342.0
50°	299.0
52.5°	264.2
55°	233.5
57.5°	210.9
60°	192.5
62.5°	174.1
65°	153.6
67.5°	135.2
70°	116.8
72.5°	100.4
75°	83.9
77.5°	67.5
80°	51.2
82.5°	36.9
85°	22.5
87.5°	10.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)