

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582299

Luminaire Tested: **HC635D010-HM63040830-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582299  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC635D010-HM63040830-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4208.9 lumens  
Efficiency: N/A  
Efficacy: 124.9 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582299

CATALOG NUMBER: HC635D010-HM63040830-61WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582299

CATALOG NUMBER: HC635D010-HM63040830-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45	45	45	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	149215
5°	151227
10°	156894
15°	170625
20°	190772
25°	200788
30°	176761
35°	122610
40°	73209
45°	34794
50°	13125
55°	5486
60°	1710
65°	1349
70°	850
75°	551
80°	821
85°	0



TEST NUMBER: P582299

CATALOG NUMBER: HC635D010-HM63040830-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	264.5	6.3
10°-20°	863.3	20.5
20°-30°	1479.2	35.1
30°-40°	1148.8	27.3
40°-50°	379.8	9.0
50°-60°	58.2	1.4
60°-70°	10.3	0.2
70°-80°	3.8	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2607.0	61.9
0°-40°	3755.8	89.2
0°-60°	4193.8	99.6
0°-90°	4208.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4208.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2722	
5°	2748	264
15°	3006	863
25°	3320	1479
35°	1832	1149
45°	449	380
55°	57	58
65°	10	10
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P582299

CATALOG NUMBER: HC635D010-HM63040830-61WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2721.9
2.5°	2719.3
5°	2748.1
7.5°	2779.3
10°	2818.5
12.5°	2896.8
15°	3006.4
17.5°	3139.5
20°	3270.1
22.5°	3345.7
25°	3319.5
27.5°	3139.5
30°	2792.4
32.5°	2325.2
35°	1832.1
37.5°	1390.9
40°	1023.0
42.5°	722.8
45°	448.8
47.5°	250.6
50°	153.9
52.5°	93.9
55°	57.4
57.5°	28.7
60°	15.6
62.5°	13.1
65°	10.4
67.5°	7.8
70°	5.3
72.5°	5.3
75°	2.6
77.5°	2.6
80°	2.6
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)