

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582294

Luminaire Tested: **HC635D010-HM63040830-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040830-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3551.3 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582294

CATALOG NUMBER: HC635D010-HM63040830-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582294

CATALOG NUMBER: HC635D010-HM63040830-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134512
5°	133876
10°	130926
15°	127855
20°	123042
25°	116366
30°	105750
35°	85595
40°	57722
45°	39663
50°	32502
55°	28443
60°	26906
65°	25398
70°	23850
75°	22664
80°	20583
85°	18052



TEST NUMBER: P582294

CATALOG NUMBER: HC635D010-HM63040830-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.7	6.5
10°-20°	632.6	17.8
20°-30°	878.9	24.7
30°-40°	782.5	22.0
40°-50°	415.4	11.7
50°-60°	271.7	7.6
60°-70°	194.7	5.5
70°-80°	112.9	3.2
80°-90°	33.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1741.2	49.0
0°-40°	2523.7	71.1
0°-60°	3210.8	90.4
0°-90°	3551.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3551.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2454	
5°	2433	230
15°	2253	633
25°	1924	879
35°	1279	783
45°	512	415
55°	298	272
65°	196	195
75°	107	113
85°	29	33
90°	0	



TEST NUMBER: P582294

CATALOG NUMBER: HC635D010-HM63040830-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2453.7
2.5°	2440.7
5°	2432.8
7.5°	2404.1
10°	2352.0
12.5°	2304.9
15°	2252.8
17.5°	2187.4
20°	2109.1
22.5°	2020.4
25°	1923.8
27.5°	1811.5
30°	1670.6
32.5°	1501.0
35°	1279.0
37.5°	1033.7
40°	806.6
42.5°	626.4
45°	511.6
47.5°	435.9
50°	381.1
52.5°	336.7
55°	297.6
57.5°	268.9
60°	245.4
62.5°	221.8
65°	195.8
67.5°	172.2
70°	148.8
72.5°	127.9
75°	107.0
77.5°	86.1
80°	65.2
82.5°	47.0
85°	28.7
87.5°	13.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)