

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581570

Luminaire Tested: **HC610D010-HM60525830-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC610D010-HM60525830-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1105.9 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581570

CATALOG NUMBER: HC610D010-HM60525830-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P581570

CATALOG NUMBER: HC610D010-HM60525830-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55385
5°	55343
10°	54764
15°	53667
20°	50830
25°	45904
30°	38993
35°	28790
40°	16645
45°	8838
50°	4989
55°	2609
60°	1710
65°	1219
70°	866
75°	678
80°	505
85°	503



TEST NUMBER: P581570

CATALOG NUMBER: HC610D010-HM60525830-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	8.6
10°-20°	264.5	23.9
20°-30°	345.2	31.2
30°-40°	263.8	23.9
40°-50°	95.5	8.6
50°-60°	27.7	2.5
60°-70°	9.9	0.9
70°-80°	3.4	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.9	63.7
0°-40°	968.7	87.6
0°-60°	1091.9	98.7
0°-90°	1105.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1105.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1010	
5°	1006	95
15°	946	264
25°	759	345
35°	430	264
45°	114	96
55°	27	28
65°	9	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P581570

CATALOG NUMBER: HC610D010-HM60525830-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1010.3
2.5°	1005.7
5°	1005.7
7.5°	998.7
10°	983.8
12.5°	966.6
15°	945.6
17.5°	914.3
20°	871.3
22.5°	818.2
25°	758.9
27.5°	691.8
30°	616.0
32.5°	530.9
35°	430.2
37.5°	324.8
40°	232.6
42.5°	160.9
45°	114.0
47.5°	82.0
50°	58.5
52.5°	41.4
55°	27.3
57.5°	19.5
60°	15.6
62.5°	12.5
65°	9.4
67.5°	7.8
70°	5.4
72.5°	3.8
75°	3.2
77.5°	2.4
80°	1.6
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)