

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581575

Luminaire Tested: **HC610D010-HM60525830-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC610D010-HM60525830-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1105.2 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581575

CATALOG NUMBER: HC610D010-HM60525830-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581575

CATALOG NUMBER: HC610D010-HM60525830-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 92 | 90 | 88 | | | |
| 2 | 103 | 96 | 91 | 86 | 101 | 95 | 90 | 85 | 91 | 87 | 83 | 88 | 85 | 82 | 85 | 82 | 80 | 78 | | | |
| 3 | 96 | 87 | 81 | 75 | 94 | 86 | 80 | 75 | 83 | 78 | 73 | 80 | 76 | 72 | 78 | 74 | 71 | 69 | | | |
| 4 | 89 | 80 | 72 | 67 | 87 | 78 | 72 | 66 | 76 | 70 | 65 | 74 | 69 | 65 | 72 | 67 | 64 | 62 | | | |
| 5 | 84 | 73 | 65 | 60 | 82 | 72 | 65 | 59 | 70 | 64 | 59 | 68 | 63 | 58 | 66 | 62 | 58 | 56 | | | |
| 6 | 78 | 67 | 59 | 54 | 77 | 66 | 59 | 54 | 64 | 58 | 53 | 63 | 57 | 53 | 61 | 56 | 53 | 51 | | | |
| 7 | 73 | 62 | 54 | 49 | 72 | 61 | 54 | 49 | 60 | 53 | 49 | 58 | 53 | 48 | 57 | 52 | 48 | 46 | | | |
| 8 | 69 | 57 | 50 | 45 | 68 | 57 | 50 | 45 | 56 | 49 | 45 | 54 | 49 | 44 | 53 | 48 | 44 | 43 | | | |
| 9 | 65 | 53 | 46 | 41 | 64 | 53 | 46 | 41 | 52 | 46 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 39 | | | |
| 10 | 62 | 50 | 43 | 38 | 60 | 49 | 43 | 38 | 49 | 42 | 38 | 48 | 42 | 38 | 47 | 42 | 38 | 36 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 39498 |
| 5° | 39390 |
| 10° | 38805 |
| 15° | 38190 |
| 20° | 36934 |
| 25° | 35173 |
| 30° | 32119 |
| 35° | 25859 |
| 40° | 17433 |
| 45° | 12707 |
| 50° | 10985 |
| 55° | 9921 |
| 60° | 9418 |
| 65° | 8911 |
| 70° | 8383 |
| 75° | 7943 |
| 80° | 7387 |
| 85° | 6919 |



TEST NUMBER: P581575

CATALOG NUMBER: HC610D010-HM60525830-61PSMDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 67.7 | 6.1 |
| 10°-20° | 189.0 | 17.1 |
| 20°-30° | 265.5 | 24.0 |
| 30°-40° | 236.3 | 21.4 |
| 40°-50° | 132.1 | 12.0 |
| 50°-60° | 94.1 | 8.5 |
| 60°-70° | 68.5 | 6.2 |
| 70°-80° | 39.7 | 3.6 |
| 80°-90° | 12.3 | 1.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 522.2 | 47.3 |
| 0°-40° | 758.5 | 68.6 |
| 0°-60° | 984.7 | 89.1 |
| 0°-90° | 1105.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1105.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 720 | |
| 5° | 716 | 68 |
| 15° | 673 | 189 |
| 25° | 582 | 265 |
| 35° | 386 | 236 |
| 45° | 164 | 132 |
| 55° | 104 | 94 |
| 65° | 69 | 68 |
| 75° | 38 | 40 |
| 85° | 11 | 12 |
| 90° | 0 | |



TEST NUMBER: P581575

CATALOG NUMBER: HC610D010-HM60525830-61PSMDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 720.5 |
| 2.5° | 717.3 |
| 5° | 715.8 |
| 7.5° | 709.5 |
| 10° | 697.1 |
| 12.5° | 685.4 |
| 15° | 672.9 |
| 17.5° | 655.8 |
| 20° | 633.1 |
| 22.5° | 608.1 |
| 25° | 581.5 |
| 27.5° | 548.8 |
| 30° | 507.4 |
| 32.5° | 454.3 |
| 35° | 386.4 |
| 37.5° | 309.9 |
| 40° | 243.6 |
| 42.5° | 194.4 |
| 45° | 163.9 |
| 47.5° | 143.7 |
| 50° | 128.8 |
| 52.5° | 115.6 |
| 55° | 103.8 |
| 57.5° | 94.4 |
| 60° | 85.9 |
| 62.5° | 78.1 |
| 65° | 68.7 |
| 67.5° | 60.9 |
| 70° | 52.3 |
| 72.5° | 44.5 |
| 75° | 37.5 |
| 77.5° | 30.5 |
| 80° | 23.4 |
| 82.5° | 17.2 |
| 85° | 11.0 |
| 87.5° | 5.4 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)