

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581662

Luminaire Tested: **HC610D010-HM60525935-61NDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581662  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC610D010-HM60525935-61NDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1072.7 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581662

CATALOG NUMBER: HC610D010-HM60525935-61NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581662

CATALOG NUMBER: HC610D010-HM60525935-61NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			
5	93	85	79	75	91	84	78	75	82	77	74	80	76	73	79	75	73	71			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	63	60	67	63	60	59			
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64063
5°	64186
10°	65246
15°	65715
20°	60077
25°	47204
30°	34556
35°	24514
40°	11593
45°	4427
50°	1979
55°	545
60°	241
65°	182
70°	112
75°	148
80°	0
85°	0



TEST NUMBER: P581662

CATALOG NUMBER: HC610D010-HM60525935-61NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.6	10.4
10°-20°	320.0	29.8
20°-30°	356.0	33.2
30°-40°	222.4	20.7
40°-50°	52.9	4.9
50°-60°	7.6	0.7
60°-70°	1.6	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.6	73.4
0°-40°	1010.0	94.2
0°-60°	1070.5	99.8
0°-90°	1072.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1072.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1169	
5°	1166	112
15°	1158	320
25°	780	356
35°	366	222
45°	57	53
55°	6	8
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581662

CATALOG NUMBER: HC610D010-HM60525935-61NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1168.6
2.5°	1163.6
5°	1166.4
7.5°	1170.6
10°	1172.1
12.5°	1171.3
15°	1157.9
17.5°	1112.9
20°	1029.8
22.5°	912.8
25°	780.4
27.5°	653.6
30°	545.9
32.5°	456.4
35°	366.3
37.5°	269.1
40°	162.0
42.5°	93.7
45°	57.1
47.5°	36.7
50°	23.2
52.5°	13.4
55°	5.7
57.5°	2.8
60°	2.2
62.5°	2.2
65°	1.4
67.5°	1.4
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)