

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581706

Luminaire Tested: **HC615D010-HM60525827-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581706  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC615D010-HM60525827-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1466.5 lumens  
Efficiency: N/A  
Efficacy: 104.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581706

CATALOG NUMBER: HC615D010-HM60525827-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581706

CATALOG NUMBER: HC615D010-HM60525827-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	57430
5°	57814
10°	58483
15°	59683
20°	60019
25°	58140
30°	52749
35°	42884
40°	28468
45°	15847
50°	8887
55°	4922
60°	2730
65°	2062
70°	1443
75°	1059
80°	600
85°	629



TEST NUMBER: P581706

CATALOG NUMBER: HC615D010-HM60525827-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.3	6.8
10°-20°	296.5	20.2
20°-30°	437.0	29.8
30°-40°	390.9	26.7
40°-50°	169.6	11.6
50°-60°	49.8	3.4
60°-70°	15.9	1.1
70°-80°	5.6	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.8	56.9
0°-40°	1224.7	83.5
0°-60°	1444.1	98.5
0°-90°	1466.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1466.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1048	
5°	1051	100
15°	1052	297
25°	961	437
35°	641	391
45°	204	170
55°	52	50
65°	16	16
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P581706

CATALOG NUMBER: HC615D010-HM60525827-61WDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1047.6
2.5°	1044.7
5°	1050.6
7.5°	1052.5
10°	1050.6
12.5°	1050.6
15°	1051.6
17.5°	1045.6
20°	1028.8
22.5°	999.9
25°	961.2
27.5°	906.8
30°	833.3
32.5°	746.0
35°	640.8
37.5°	520.9
40°	397.8
42.5°	290.7
45°	204.4
47.5°	145.8
50°	104.2
52.5°	74.5
55°	51.5
57.5°	34.7
60°	24.9
62.5°	19.9
65°	15.9
67.5°	11.9
70°	9.0
72.5°	6.9
75°	5.0
77.5°	4.0
80°	1.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)