

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581760

Luminaire Tested: **HC615D010-HM60525840-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC615D010-HM60525840-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1654.0 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581760

CATALOG NUMBER: HC615D010-HM60525840-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581760

CATALOG NUMBER: HC615D010-HM60525840-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64776
5°	65205
10°	65958
15°	67316
20°	67696
25°	65586
30°	59496
35°	48379
40°	32110
45°	17870
50°	10021
55°	5563
60°	3059
65°	2322
70°	1619
75°	1186
80°	726
85°	692



TEST NUMBER: P581760

CATALOG NUMBER: HC615D010-HM60525840-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	6.8
10°-20°	334.4	20.2
20°-30°	492.9	29.8
30°-40°	440.9	26.7
40°-50°	191.3	11.6
50°-60°	56.2	3.4
60°-70°	17.9	1.1
70°-80°	6.3	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.5	56.9
0°-40°	1381.4	83.5
0°-60°	1628.8	98.5
0°-90°	1654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1654.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1182	
5°	1185	113
15°	1186	334
25°	1084	493
35°	723	441
45°	230	191
55°	58	56
65°	18	18
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P581760

CATALOG NUMBER: HC615D010-HM60525840-61WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1181.6
2.5°	1178.2
5°	1184.9
7.5°	1187.2
10°	1184.9
12.5°	1184.9
15°	1186.1
17.5°	1179.4
20°	1160.4
22.5°	1128.0
25°	1084.3
27.5°	1022.7
30°	939.9
32.5°	841.5
35°	722.9
37.5°	587.5
40°	448.7
42.5°	327.9
45°	230.5
47.5°	164.5
50°	117.5
52.5°	83.9
55°	58.2
57.5°	39.2
60°	27.9
62.5°	22.4
65°	17.9
67.5°	13.4
70°	10.1
72.5°	7.8
75°	5.6
77.5°	4.4
80°	2.3
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)