

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582415

Luminaire Tested: **HC640D010-HM63040827-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC640D010-HM63040827-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4454.2 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582415

CATALOG NUMBER: HC640D010-HM63040827-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582415

CATALOG NUMBER: HC640D010-HM63040827-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211513
5°	214813
10°	227044
15°	252805
20°	262173
25°	215105
30°	150732
35°	102834
40°	53565
45°	18839
50°	8435
55°	2695
60°	1546
65°	1090
70°	914
75°	593
80°	0
85°	0



TEST NUMBER: P582415

CATALOG NUMBER: HC640D010-HM63040827-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.1	8.5
10°-20°	1252.7	28.1
20°-30°	1595.1	35.8
30°-40°	950.6	21.3
40°-50°	230.5	5.2
50°-60°	35.4	0.8
60°-70°	8.7	0.2
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3226.0	72.4
0°-40°	4176.6	93.8
0°-60°	4442.5	99.7
0°-90°	4454.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4454.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3858	
5°	3904	378
15°	4454	1253
25°	3556	1595
35°	1537	951
45°	243	231
55°	28	35
65°	8	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582415

CATALOG NUMBER: HC640D010-HM63040827-61MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	3858.3
2.5°	3858.3
5°	3903.6
7.5°	3974.1
10°	4078.7
12.5°	4242.6
15°	4454.4
17.5°	4587.1
20°	4494.0
22.5°	4135.2
25°	3556.2
27.5°	2917.8
30°	2381.2
32.5°	1946.2
35°	1536.6
37.5°	1132.6
40°	748.5
42.5°	403.9
45°	243.0
47.5°	152.5
50°	98.9
52.5°	59.4
55°	28.2
57.5°	16.9
60°	14.1
62.5°	11.3
65°	8.4
67.5°	5.7
70°	5.7
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)