

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581770

Luminaire Tested: **HC615D010-HM60525927-61NDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581770  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC615D010-HM60525927-61NDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1275.2 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581770

CATALOG NUMBER: HC615D010-HM60525927-61NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581770

CATALOG NUMBER: HC615D010-HM60525927-61NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76156
5°	76310
10°	77565
15°	78128
20°	71424
25°	56126
30°	41082
35°	29145
40°	13783
45°	5264
50°	2354
55°	640
60°	274
65°	221
70°	128
75°	169
80°	0
85°	0



TEST NUMBER: P581770

CATALOG NUMBER: HC615D010-HM60525927-61NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.7	10.4
10°-20°	380.5	29.8
20°-30°	423.3	33.2
30°-40°	264.4	20.7
40°-50°	62.8	4.9
50°-60°	9.0	0.7
60°-70°	1.9	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.4	73.4
0°-40°	1200.8	94.2
0°-60°	1272.6	99.8
0°-90°	1275.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1275.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1389	
5°	1387	133
15°	1377	380
25°	928	423
35°	436	264
45°	68	63
55°	7	9
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581770

CATALOG NUMBER: HC615D010-HM60525927-61NDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1389.2
2.5°	1383.3
5°	1386.7
7.5°	1391.7
10°	1393.4
12.5°	1392.6
15°	1376.6
17.5°	1323.1
20°	1224.3
22.5°	1085.3
25°	927.9
27.5°	777.1
30°	649.0
32.5°	542.6
35°	435.5
37.5°	319.8
40°	192.6
42.5°	111.3
45°	67.9
47.5°	43.6
50°	27.6
52.5°	15.9
55°	6.7
57.5°	3.4
60°	2.5
62.5°	2.5
65°	1.7
67.5°	1.7
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)