

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581806

Luminaire Tested: **HC615D010-HM60525935-61NDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581806  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC615D010-HM60525935-61NDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1465.5 lumens  
Efficiency: N/A  
Efficacy: 104.7 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581806

CATALOG NUMBER: HC615D010-HM60525935-61NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581806

CATALOG NUMBER: HC615D010-HM60525935-61NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87526
5°	87701
10°	89143
15°	89796
20°	82076
25°	64498
30°	47210
35°	33488
40°	15837
45°	6047
50°	2712
55°	736
60°	307
65°	246
70°	144
75°	191
80°	0
85°	0



TEST NUMBER: P581806

CATALOG NUMBER: HC615D010-HM60525935-61NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.5	10.4
10°-20°	437.3	29.8
20°-30°	486.4	33.2
30°-40°	303.8	20.7
40°-50°	72.2	4.9
50°-60°	10.3	0.7
60°-70°	2.1	0.1
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.2	73.4
0°-40°	1380.0	94.2
0°-60°	1462.6	99.8
0°-90°	1465.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1465.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1597	
5°	1594	152
15°	1582	437
25°	1066	486
35°	500	304
45°	78	72
55°	8	10
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581806

CATALOG NUMBER: HC615D010-HM60525935-61NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1596.6
2.5°	1589.8
5°	1593.7
7.5°	1599.4
10°	1601.4
12.5°	1600.5
15°	1582.2
17.5°	1520.6
20°	1406.9
22.5°	1247.3
25°	1066.3
27.5°	893.1
30°	745.8
32.5°	623.6
35°	500.4
37.5°	367.6
40°	221.3
42.5°	128.0
45°	78.0
47.5°	50.1
50°	31.8
52.5°	18.3
55°	7.7
57.5°	3.9
60°	2.8
62.5°	2.8
65°	1.9
67.5°	1.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)