

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582473

Luminaire Tested: **HC640D010-HM63040840-61NDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582473  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC640D010-HM63040840-61NDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4797.3 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582473

CATALOG NUMBER: HC640D010-HM63040840-61NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582473

CATALOG NUMBER: HC640D010-HM63040840-61NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	293672
5°	292427
10°	285505
15°	271017
20°	241574
25°	203492
30°	162120
35°	115670
40°	62195
45°	26646
50°	12119
55°	4425
60°	2171
65°	1712
70°	1587
75°	699
80°	1042
85°	0



TEST NUMBER: P582473

CATALOG NUMBER: HC640D010-HM63040840-61NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	501.6	10.5
10°-20°	1323.7	27.6
20°-30°	1533.1	32.0
30°-40°	1060.1	22.1
40°-50°	306.1	6.4
50°-60°	52.7	1.1
60°-70°	13.4	0.3
70°-80°	5.2	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3358.4	70.0
0°-40°	4418.5	92.1
0°-60°	4777.3	99.6
0°-90°	4797.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4797.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5357	
5°	5314	502
15°	4775	1324
25°	3364	1533
35°	1728	1060
45°	344	306
55°	46	53
65°	13	13
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P582473

CATALOG NUMBER: HC640D010-HM63040840-61NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5357.0
2.5°	5333.8
5°	5314.0
7.5°	5254.5
10°	5128.9
12.5°	4976.9
15°	4775.3
17.5°	4491.1
20°	4140.9
22.5°	3754.1
25°	3364.2
27.5°	2964.3
30°	2561.1
32.5°	2158.0
35°	1728.4
37.5°	1282.2
40°	869.1
42.5°	548.6
45°	343.7
47.5°	221.5
50°	142.1
52.5°	85.9
55°	46.3
57.5°	26.4
60°	19.8
62.5°	16.5
65°	13.2
67.5°	9.9
70°	9.9
72.5°	6.6
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)