

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582498

Luminaire Tested: **HC640D010-HM63040927-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582498
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC640D010-HM63040927-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3527.1 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582498

CATALOG NUMBER: HC640D010-HM63040927-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582498

CATALOG NUMBER: HC640D010-HM63040927-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138136
5°	139054
10°	140662
15°	143548
20°	144353
25°	139859
30°	126880
35°	103162
40°	68471
45°	38112
50°	21372
55°	11861
60°	6535
65°	4942
70°	3446
75°	2521
80°	1484
85°	1510



TEST NUMBER: P582498

CATALOG NUMBER: HC640D010-HM63040927-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.2	6.8
10°-20°	713.2	20.2
20°-30°	1051.2	29.8
30°-40°	940.2	26.7
40°-50°	407.9	11.6
50°-60°	119.9	3.4
60°-70°	38.2	1.1
70°-80°	13.5	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2005.5	56.9
0°-40°	2945.7	83.5
0°-60°	3473.5	98.5
0°-90°	3527.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3527.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2520	
5°	2527	241
15°	2529	713
25°	2312	1051
35°	1542	940
45°	492	408
55°	124	120
65°	38	38
75°	12	14
85°	2	2
90°	0	



TEST NUMBER: P582498

CATALOG NUMBER: HC640D010-HM63040927-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2519.8
2.5°	2512.7
5°	2526.9
7.5°	2531.8
10°	2526.9
12.5°	2526.9
15°	2529.3
17.5°	2515.1
20°	2474.4
22.5°	2405.3
25°	2312.2
27.5°	2181.0
30°	2004.4
32.5°	1794.4
35°	1541.5
37.5°	1252.8
40°	956.8
42.5°	699.2
45°	491.6
47.5°	350.7
50°	250.6
52.5°	179.0
55°	124.1
57.5°	83.5
60°	59.6
62.5°	47.7
65°	38.1
67.5°	28.6
70°	21.5
72.5°	16.8
75°	11.9
77.5°	9.5
80°	4.7
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)