

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582516

Luminaire Tested: **HC640D010-HM63040930-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC640D010-HM63040930-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4213.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582516

CATALOG NUMBER: HC640D010-HM63040930-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582516

CATALOG NUMBER: HC640D010-HM63040930-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164998
5°	166101
10°	168022
15°	171465
20°	172425
25°	167060
30°	151549
35°	123219
40°	81789
45°	45516
50°	25526
55°	14174
60°	7806
65°	5915
70°	4103
75°	3008
80°	1799
85°	1824



TEST NUMBER: P582516

CATALOG NUMBER: HC640D010-HM63040930-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.1	6.8
10°-20°	851.9	20.2
20°-30°	1255.6	29.8
30°-40°	1123.0	26.7
40°-50°	487.2	11.6
50°-60°	143.2	3.4
60°-70°	45.7	1.1
70°-80°	16.1	0.4
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2395.6	56.9
0°-40°	3518.6	83.5
0°-60°	4148.9	98.5
0°-90°	4213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4213.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3010	
5°	3018	288
15°	3021	852
25°	2762	1256
35°	1841	1123
45°	587	487
55°	148	143
65°	46	46
75°	14	16
85°	3	2
90°	0	



TEST NUMBER: P582516

CATALOG NUMBER: HC640D010-HM63040930-61WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3009.8
2.5°	3001.3
5°	3018.4
7.5°	3024.1
10°	3018.4
12.5°	3018.4
15°	3021.2
17.5°	3004.2
20°	2955.6
22.5°	2873.0
25°	2761.9
27.5°	2605.2
30°	2394.1
32.5°	2143.4
35°	1841.2
37.5°	1496.4
40°	1142.9
42.5°	835.1
45°	587.1
47.5°	419.0
50°	299.3
52.5°	213.8
55°	148.3
57.5°	99.7
60°	71.2
62.5°	57.0
65°	45.6
67.5°	34.2
70°	25.6
72.5°	19.9
75°	14.2
77.5°	11.3
80°	5.7
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)