

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582517

Luminaire Tested: **HC640D010-HM63040930-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582517  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC640D010-HM63040930-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4158.9 lumens  
Efficiency: N/A  
Efficacy: 101.4 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582517

CATALOG NUMBER: HC640D010-HM63040930-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582517

CATALOG NUMBER: HC640D010-HM63040930-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	141924
5°	141839
10°	140467
15°	139013
20°	135083
25°	129376
30°	120075
35°	103302
40°	75406
45°	51672
50°	41534
55°	36204
60°	33407
65°	31767
70°	29684
75°	27747
80°	25193
85°	21511



TEST NUMBER: P582517

CATALOG NUMBER: HC640D010-HM63040930-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.3	5.9
10°-20°	687.9	16.5
20°-30°	978.3	23.5
30°-40°	941.9	22.6
40°-50°	541.9	13.0
50°-60°	343.4	8.3
60°-70°	243.0	5.8
70°-80°	138.6	3.3
80°-90°	39.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1910.6	45.9
0°-40°	2852.5	68.6
0°-60°	3737.8	89.9
0°-90°	4158.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4158.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2589	
5°	2578	244
15°	2449	688
25°	2139	978
35°	1544	942
45°	666	542
55°	379	343
65°	245	243
75°	131	139
85°	34	40
90°	0	



TEST NUMBER: P582517

CATALOG NUMBER: HC640D010-HM63040930-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2588.9
2.5°	2577.5
5°	2577.5
7.5°	2560.4
10°	2523.4
12.5°	2486.3
15°	2449.4
17.5°	2392.4
20°	2315.5
22.5°	2230.0
25°	2138.9
27.5°	2027.8
30°	1896.9
32.5°	1737.4
35°	1543.6
37.5°	1307.3
40°	1053.7
42.5°	831.6
45°	666.5
47.5°	561.1
50°	487.0
52.5°	427.2
55°	378.8
57.5°	336.1
60°	304.7
62.5°	276.2
65°	244.9
67.5°	216.4
70°	185.2
72.5°	156.7
75°	131.0
77.5°	105.4
80°	79.8
82.5°	57.0
85°	34.2
87.5°	14.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)