

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582544

Luminaire Tested: **HC640D010-HM63040940-61NDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582544  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC640D010-HM63040940-61NDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4388.0 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582544

CATALOG NUMBER: HC640D010-HM63040940-61NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582544

CATALOG NUMBER: HC640D010-HM63040940-61NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	262051
5°	262579
10°	266896
15°	268838
20°	245756
25°	193106
30°	141357
35°	100271
40°	47425
45°	18087
50°	8111
55°	2208
60°	954
65°	752
70°	465
75°	614
80°	0
85°	0



TEST NUMBER: P582544

CATALOG NUMBER: HC640D010-HM63040940-61NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	456.5	10.4
10°-20°	1309.3	29.8
20°-30°	1456.3	33.2
30°-40°	909.8	20.7
40°-50°	216.1	4.9
50°-60°	30.9	0.7
60°-70°	6.4	0.1
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3222.0	73.4
0°-40°	4131.8	94.2
0°-60°	4378.8	99.8
0°-90°	4388.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4388.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4780	
5°	4772	456
15°	4737	1309
25°	3192	1456
35°	1498	910
45°	233	216
55°	23	31
65°	6	6
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582544

CATALOG NUMBER: HC640D010-HM63040940-61NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4780.2
2.5°	4760.0
5°	4771.6
7.5°	4788.9
10°	4794.6
12.5°	4791.7
15°	4736.9
17.5°	4552.5
20°	4212.6
22.5°	3734.2
25°	3192.5
27.5°	2673.9
30°	2233.1
32.5°	1867.2
35°	1498.3
37.5°	1100.7
40°	662.7
42.5°	383.2
45°	233.3
47.5°	149.8
50°	95.1
52.5°	54.7
55°	23.1
57.5°	11.5
60°	8.7
62.5°	8.7
65°	5.8
67.5°	5.8
70°	2.9
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)