

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581983

Luminaire Tested: **HC625D010-HM60525827-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581983  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525827-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2617.4 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581983

CATALOG NUMBER: HC625D010-HM60525827-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581983

CATALOG NUMBER: HC625D010-HM60525827-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61		
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124299
5°	126238
10°	133425
15°	148559
20°	154066
25°	126413
30°	88583
35°	60432
40°	31480
45°	11063
50°	4955
55°	1577
60°	910
65°	649
70°	529
75°	339
80°	0
85°	0



TEST NUMBER: P581983

CATALOG NUMBER: HC625D010-HM60525827-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	222.2	8.5
10°-20°	736.2	28.1
20°-30°	937.4	35.8
30°-40°	558.7	21.3
40°-50°	135.4	5.2
50°-60°	20.7	0.8
60°-70°	5.1	0.2
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1895.8	72.4
0°-40°	2454.4	93.8
0°-60°	2610.6	99.7
0°-90°	2617.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2617.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2267	
5°	2294	222
15°	2618	736
25°	2090	937
35°	903	559
45°	143	135
55°	16	21
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P581983

CATALOG NUMBER: HC625D010-HM60525827-61MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2267.4
2.5°	2267.4
5°	2294.0
7.5°	2335.5
10°	2396.9
12.5°	2493.2
15°	2617.6
17.5°	2695.7
20°	2640.9
22.5°	2430.1
25°	2089.9
27.5°	1714.7
30°	1399.4
32.5°	1143.7
35°	903.0
37.5°	665.6
40°	439.9
42.5°	237.3
45°	142.7
47.5°	89.6
50°	58.1
52.5°	34.8
55°	16.5
57.5°	9.9
60°	8.3
62.5°	6.6
65°	5.0
67.5°	3.3
70°	3.3
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)