

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582633

Luminaire Tested: **HC645D010-HM64560927-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC645D010-HM64560927-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3503.7 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582633

CATALOG NUMBER: HC645D010-HM64560927-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582633

CATALOG NUMBER: HC645D010-HM64560927-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130428
5°	129952
10°	127775
15°	125529
20°	121192
25°	114914
30°	104522
35°	83520
40°	55719
45°	39725
50°	33091
55°	28845
60°	27257
65°	25671
70°	23578
75°	22028
80°	20047
85°	17549



TEST NUMBER: P582633

CATALOG NUMBER: HC645D010-HM64560927-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.3	6.4
10°-20°	621.0	17.7
20°-30°	867.8	24.8
30°-40°	764.5	21.8
40°-50°	413.0	11.8
50°-60°	276.1	7.9
60°-70°	195.7	5.6
70°-80°	110.1	3.1
80°-90°	32.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1712.2	48.9
0°-40°	2476.6	70.7
0°-60°	3165.8	90.4
0°-90°	3503.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3503.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2379	
5°	2362	223
15°	2212	621
25°	1900	868
35°	1248	764
45°	512	413
55°	302	276
65°	198	196
75°	104	110
85°	28	32
90°	0	



TEST NUMBER: P582633

CATALOG NUMBER: HC645D010-HM64560927-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2379.2
2.5°	2366.5
5°	2361.5
7.5°	2338.6
10°	2295.4
12.5°	2254.9
15°	2211.8
17.5°	2153.4
20°	2077.4
22.5°	1993.6
25°	1899.8
27.5°	1790.7
30°	1651.2
32.5°	1478.8
35°	1248.0
37.5°	996.8
40°	778.6
42.5°	613.8
45°	512.4
47.5°	443.9
50°	388.0
52.5°	342.4
55°	301.8
57.5°	273.9
60°	248.6
62.5°	223.2
65°	197.9
67.5°	172.4
70°	147.1
72.5°	124.3
75°	104.0
77.5°	83.8
80°	63.5
82.5°	45.6
85°	27.9
87.5°	12.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)