

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582005

Luminaire Tested: **HC625D010-HM60525830-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC625D010-HM60525830-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2592.2 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582005
CATALOG NUMBER: HC625D010-HM60525830-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P582005

CATALOG NUMBER: HC625D010-HM60525830-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158671
5°	157995
10°	154256
15°	146437
20°	130526
25°	109948
30°	87596
35°	62499
40°	33606
45°	14397
50°	6550
55°	2399
60°	1184
65°	921
70°	866
75°	381
80°	568
85°	0



TEST NUMBER: P582005

CATALOG NUMBER: HC625D010-HM60525830-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.0	10.5
10°-20°	715.2	27.6
20°-30°	828.3	32.0
30°-40°	572.8	22.1
40°-50°	165.4	6.4
50°-60°	28.5	1.1
60°-70°	7.3	0.3
70°-80°	2.8	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1814.6	70.0
0°-40°	2387.3	92.1
0°-60°	2581.3	99.6
0°-90°	2592.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2592.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2894	
5°	2871	271
15°	2580	715
25°	1818	828
35°	934	573
45°	186	165
55°	25	29
65°	7	7
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P582005

CATALOG NUMBER: HC625D010-HM60525830-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2894.4
2.5°	2881.9
5°	2871.1
7.5°	2839.0
10°	2771.1
12.5°	2689.1
15°	2580.2
17.5°	2426.6
20°	2237.4
22.5°	2028.4
25°	1817.7
27.5°	1601.6
30°	1383.8
32.5°	1165.9
35°	933.9
37.5°	692.8
40°	469.6
42.5°	296.5
45°	185.7
47.5°	119.7
50°	76.8
52.5°	46.5
55°	25.1
57.5°	14.3
60°	10.8
62.5°	8.9
65°	7.1
67.5°	5.4
70°	5.4
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)