

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582036

Luminaire Tested: **HC6R25D010-HM60525835-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R25D010-HM60525835-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2858.6 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582036

CATALOG NUMBER: HC6R25D010-HM60525835-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582036

CATALOG NUMBER: HC6R25D010-HM60525835-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132594
5°	135488
10°	143629
15°	160546
20°	168090
25°	140149
30°	98091
35°	66060
40°	34021
45°	11815
50°	5254
55°	1739
60°	800
65°	700
70°	577
75°	381
80°	568
85°	0



TEST NUMBER: P582036

CATALOG NUMBER: HC6R25D010-HM60525835-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.7	8.3
10°-20°	797.0	27.9
20°-30°	1035.8	36.2
30°-40°	611.9	21.4
40°-50°	146.0	5.1
50°-60°	21.5	0.8
60°-70°	5.4	0.2
70°-80°	2.1	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2071.5	72.5
0°-40°	2683.4	93.9
0°-60°	2850.8	99.7
0°-90°	2858.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2858.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2419	
5°	2462	239
15°	2829	797
25°	2317	1036
35°	987	612
45°	152	146
55°	18	21
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582036

CATALOG NUMBER: HC6R25D010-HM60525835-62RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2418.7
2.5°	2424.1
5°	2462.1
7.5°	2511.1
10°	2580.2
12.5°	2689.1
15°	2828.8
17.5°	2923.1
20°	2881.3
22.5°	2670.9
25°	2317.0
27.5°	1912.5
30°	1549.6
32.5°	1253.8
35°	987.1
37.5°	725.7
40°	475.4
42.5°	259.5
45°	152.4
47.5°	94.4
50°	61.6
52.5°	36.3
55°	18.2
57.5°	9.0
60°	7.3
62.5°	7.3
65°	5.4
67.5°	3.6
70°	3.6
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)