

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582724

Luminaire Tested: **HC650D010-HM64560830-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC650D010-HM64560830-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5310.9 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582724

CATALOG NUMBER: HC650D010-HM64560830-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582724

CATALOG NUMBER: HC650D010-HM64560830-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	317168
5°	317807
10°	323035
15°	325393
20°	297444
25°	233729
30°	171083
35°	121358
40°	57400
45°	21901
50°	9808
55°	2667
60°	1151
65°	908
70°	561
75°	741
80°	0
85°	0



TEST NUMBER: P582724

CATALOG NUMBER: HC650D010-HM64560830-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.5	10.4
10°-20°	1584.7	29.8
20°-30°	1762.6	33.2
30°-40°	1101.1	20.7
40°-50°	261.6	4.9
50°-60°	37.4	0.7
60°-70°	7.8	0.1
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3899.8	73.4
0°-40°	5000.9	94.2
0°-60°	5299.9	99.8
0°-90°	5310.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5310.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5786	
5°	5775	552
15°	5733	1585
25°	3864	1763
35°	1813	1101
45°	282	262
55°	28	37
65°	7	8
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P582724

CATALOG NUMBER: HC650D010-HM64560830-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	5785.6
2.5°	5761.3
5°	5775.2
7.5°	5796.1
10°	5803.1
12.5°	5799.7
15°	5733.4
17.5°	5510.2
20°	5098.6
22.5°	4519.7
25°	3864.1
27.5°	3236.3
30°	2702.7
32.5°	2259.8
35°	1813.4
37.5°	1332.2
40°	802.1
42.5°	463.8
45°	282.5
47.5°	181.4
50°	115.0
52.5°	66.3
55°	27.9
57.5°	13.9
60°	10.5
62.5°	10.5
65°	7.0
67.5°	7.0
70°	3.5
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)