

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582750

Luminaire Tested: **HC650D010-HM64560835-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582750  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC650D010-HM64560835-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5388.9 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582750

CATALOG NUMBER: HC650D010-HM64560835-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582750

CATALOG NUMBER: HC650D010-HM64560835-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	211047
5°	212458
10°	214915
15°	219326
20°	220554
25°	213684
30°	193846
35°	157617
40°	104625
45°	58223
50°	32647
55°	18121
60°	9999
65°	7562
70°	5257
75°	3855
80°	2305
85°	2327



TEST NUMBER: P582750

CATALOG NUMBER: HC650D010-HM64560835-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	368.5	6.8
10°-20°	1089.6	20.2
20°-30°	1606.0	29.8
30°-40°	1436.5	26.7
40°-50°	623.2	11.6
50°-60°	183.1	3.4
60°-70°	58.4	1.1
70°-80°	20.6	0.4
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3064.1	56.9
0°-40°	4500.6	83.5
0°-60°	5306.9	98.5
0°-90°	5388.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5388.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3850	
5°	3861	369
15°	3864	1090
25°	3533	1606
35°	2355	1436
45°	751	623
55°	190	183
65°	58	58
75°	18	21
85°	4	3
90°	0	



TEST NUMBER: P582750

CATALOG NUMBER: HC650D010-HM64560835-61WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3849.8
2.5°	3839.0
5°	3860.8
7.5°	3868.1
10°	3860.8
12.5°	3860.8
15°	3864.5
17.5°	3842.5
20°	3780.6
22.5°	3674.8
25°	3532.7
27.5°	3332.2
30°	3062.3
32.5°	2741.6
35°	2355.2
37.5°	1913.9
40°	1462.0
42.5°	1068.2
45°	751.0
47.5°	535.9
50°	382.8
52.5°	273.4
55°	189.6
57.5°	127.5
60°	91.2
62.5°	72.9
65°	58.3
67.5°	43.7
70°	32.8
72.5°	25.5
75°	18.2
77.5°	14.5
80°	7.3
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)