

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582082

Luminaire Tested: **HC625D010-HM60525930-61WDBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC625D010-HM60525930-61WDBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2019.8 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582082

CATALOG NUMBER: HC625D010-HM60525930-61WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P582082

CATALOG NUMBER: HC625D010-HM60525930-61WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92
2	107	101	97	93	104	100	95	92	96	93	90	93	91	88	90	88	86	85			85
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	95	86	80	75	93	85	79	75	83	78	74	81	77	73	79	75	72	71			71
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65			65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	44	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71738
5°	72259
10°	73523
15°	76436
20°	79649
25°	82481
30°	81386
35°	67806
40°	43481
45°	21708
50°	8614
55°	2925
60°	833
65°	597
70°	481
75°	635
80°	474
85°	0



TEST NUMBER: P582082

CATALOG NUMBER: HC625D010-HM60525930-61WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	6.2
10°-20°	382.0	18.9
20°-30°	623.7	30.9
30°-40°	611.4	30.3
40°-50°	234.4	11.6
50°-60°	34.4	1.7
60°-70°	5.1	0.3
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1131.3	56.0
0°-40°	1742.8	86.3
0°-60°	2011.6	99.6
0°-90°	2019.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2019.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1309	
5°	1313	126
15°	1347	382
25°	1364	624
35°	1013	611
45°	280	234
55°	31	34
65°	5	5
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P582082

CATALOG NUMBER: HC625D010-HM60525930-61WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1308.6
2.5°	1305.5
5°	1313.1
7.5°	1317.8
10°	1320.8
12.5°	1331.6
15°	1346.8
17.5°	1359.1
20°	1365.3
22.5°	1366.8
25°	1363.6
27.5°	1342.2
30°	1285.7
32.5°	1178.4
35°	1013.2
37.5°	809.7
40°	607.6
42.5°	433.2
45°	280.0
47.5°	171.4
50°	101.0
52.5°	58.1
55°	30.6
57.5°	13.8
60°	7.6
62.5°	6.1
65°	4.6
67.5°	4.6
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)