

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582794

Luminaire Tested: **HC650D010-HM64560930-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582794
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC650D010-HM64560930-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4545.4 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582794

CATALOG NUMBER: HC650D010-HM64560930-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P582794

CATALOG NUMBER: HC650D010-HM64560930-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227646
5°	227459
10°	225085
15°	220563
20°	208933
25°	188678
30°	160284
35°	118333
40°	68443
45°	36322
50°	20528
55°	10733
60°	7028
65°	4994
70°	3590
75°	2732
80°	2020
85°	2013



TEST NUMBER: P582794

CATALOG NUMBER: HC650D010-HM64560930-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.7	8.6
10°-20°	1087.0	23.9
20°-30°	1418.7	31.2
30°-40°	1084.2	23.9
40°-50°	392.5	8.6
50°-60°	114.0	2.5
60°-70°	40.8	0.9
70°-80°	14.0	0.3
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2897.4	63.7
0°-40°	3981.5	87.6
0°-60°	4488.0	98.7
0°-90°	4545.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4545.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4153	
5°	4133	392
15°	3886	1087
25°	3119	1419
35°	1768	1084
45°	468	393
55°	112	114
65°	38	41
75°	13	14
85°	3	3
90°	0	



TEST NUMBER: P582794

CATALOG NUMBER: HC650D010-HM64560930-61MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4152.6
2.5°	4133.4
5°	4133.4
7.5°	4104.4
10°	4043.5
12.5°	3972.9
15°	3886.3
17.5°	3757.9
20°	3581.4
22.5°	3363.1
25°	3119.3
27.5°	2843.3
30°	2532.1
32.5°	2182.3
35°	1768.2
37.5°	1335.0
40°	956.4
42.5°	661.1
45°	468.5
47.5°	336.9
50°	240.7
52.5°	170.1
55°	112.3
57.5°	80.2
60°	64.1
62.5°	51.4
65°	38.5
67.5°	32.1
70°	22.4
72.5°	16.1
75°	12.9
77.5°	9.7
80°	6.4
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)