

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582889

Luminaire Tested: **HC605D010-HM60525835-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC605D010-HM60525835-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 686.9 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582889

CATALOG NUMBER: HC605D010-HM60525835-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582889

CATALOG NUMBER: HC605D010-HM60525835-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24548
5°	24483
10°	24114
15°	23735
20°	22956
25°	21866
30°	19965
35°	16068
40°	10835
45°	7900
50°	6823
55°	6165
60°	5844
65°	5539
70°	5209
75°	4935
80°	4609
85°	4277



TEST NUMBER: P582889

CATALOG NUMBER: HC605D010-HM60525835-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.1	6.1
10°-20°	117.4	17.1
20°-30°	165.0	24.0
30°-40°	146.9	21.4
40°-50°	82.1	12.0
50°-60°	58.5	8.5
60°-70°	42.6	6.2
70°-80°	24.6	3.6
80°-90°	7.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.6	47.3
0°-40°	471.5	68.6
0°-60°	612.0	89.1
0°-90°	686.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	448	
5°	445	42
15°	418	117
25°	362	165
35°	240	147
45°	102	82
55°	64	58
65°	43	43
75°	23	25
85°	7	8
90°	0	



TEST NUMBER: P582889

CATALOG NUMBER: HC605D010-HM60525835-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	447.8
2.5°	445.9
5°	444.9
7.5°	441.0
10°	433.2
12.5°	426.0
15°	418.2
17.5°	407.6
20°	393.5
22.5°	378.0
25°	361.5
27.5°	341.0
30°	315.4
32.5°	282.4
35°	240.1
37.5°	192.7
40°	151.4
42.5°	120.8
45°	101.9
47.5°	89.3
50°	80.0
52.5°	71.8
55°	64.5
57.5°	58.8
60°	53.3
62.5°	48.5
65°	42.7
67.5°	37.9
70°	32.5
72.5°	27.7
75°	23.3
77.5°	18.9
80°	14.6
82.5°	10.6
85°	6.8
87.5°	3.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)