

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582198

Luminaire Tested: **HC6R30D010-HM63040840-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R30D010-HM63040840-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3774.1 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582198

CATALOG NUMBER: HC6R30D010-HM63040840-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582198

CATALOG NUMBER: HC6R30D010-HM63040840-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	175057
5°	178885
10°	189626
15°	211954
20°	221931
25°	185043
30°	129501
35°	87207
40°	44920
45°	15599
50°	6942
55°	2284
60°	1053
65°	921
70°	769
75°	508
80°	758
85°	0



TEST NUMBER: P582198

CATALOG NUMBER: HC6R30D010-HM63040840-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.1	8.3
10°-20°	1052.3	27.9
20°-30°	1367.6	36.2
30°-40°	807.8	21.4
40°-50°	192.7	5.1
50°-60°	28.4	0.8
60°-70°	7.1	0.2
70°-80°	2.9	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2734.9	72.5
0°-40°	3542.7	93.9
0°-60°	3763.8	99.7
0°-90°	3774.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3774.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3193	
5°	3251	315
15°	3735	1052
25°	3059	1368
35°	1303	808
45°	201	193
55°	24	28
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P582198

CATALOG NUMBER: HC6R30D010-HM63040840-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3193.3
2.5°	3200.4
5°	3250.7
7.5°	3315.4
10°	3406.5
12.5°	3550.2
15°	3734.6
17.5°	3859.3
20°	3804.2
22.5°	3526.2
25°	3059.2
27.5°	2525.0
30°	2045.8
32.5°	1655.3
35°	1303.1
37.5°	958.2
40°	627.7
42.5°	342.6
45°	201.2
47.5°	124.6
50°	81.4
52.5°	47.9
55°	23.9
57.5°	12.0
60°	9.6
62.5°	9.6
65°	7.1
67.5°	4.8
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)