

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582216

Luminaire Tested: **HC6R30D010-HM63040927-62RMDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582216  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC6R30D010-HM63040927-62RMDC  
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2724.2 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582216

CATALOG NUMBER: HC6R30D010-HM63040927-62RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582216

CATALOG NUMBER: HC6R30D010-HM63040927-62RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126360
5°	129127
10°	136877
15°	152992
20°	160191
25°	133562
30°	93476
35°	62948
40°	32418
45°	11265
50°	5006
55°	1644
60°	757
65°	675
70°	545
75°	381
80°	568
85°	0



TEST NUMBER: P582216

CATALOG NUMBER: HC6R30D010-HM63040927-62RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	227.4	8.3
10°-20°	759.5	27.9
20°-30°	987.1	36.2
30°-40°	583.1	21.4
40°-50°	139.1	5.1
50°-60°	20.5	0.8
60°-70°	5.1	0.2
70°-80°	2.1	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1974.1	72.5
0°-40°	2557.2	93.9
0°-60°	2716.7	99.7
0°-90°	2724.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2724.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2305	
5°	2346	227
15°	2696	760
25°	2208	987
35°	941	583
45°	145	139
55°	17	20
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582216

CATALOG NUMBER: HC6R30D010-HM63040927-62RMDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2305.0
2.5°	2310.1
5°	2346.5
7.5°	2393.1
10°	2458.9
12.5°	2562.7
15°	2695.7
17.5°	2785.7
20°	2745.9
22.5°	2545.3
25°	2208.1
27.5°	1822.5
30°	1476.7
32.5°	1194.8
35°	940.6
37.5°	691.6
40°	453.0
42.5°	247.3
45°	145.3
47.5°	89.9
50°	58.7
52.5°	34.6
55°	17.2
57.5°	8.7
60°	6.9
62.5°	6.9
65°	5.2
67.5°	3.4
70°	3.4
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)