

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582202

Luminaire Tested: **HC630D010-HM63040927-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC630D010-HM63040927-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2632.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582202

CATALOG NUMBER: HC630D010-HM63040927-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582202

CATALOG NUMBER: HC630D010-HM63040927-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			76
5	93	85	79	75	91	84	78	75	82	77	74	80	76	73	79	75	73	71			71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157224
5°	157539
10°	160123
15°	161289
20°	147439
25°	115857
30°	84811
35°	60157
40°	28453
45°	10862
50°	4870
55°	1319
60°	570
65°	441
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P582202

CATALOG NUMBER: HC630D010-HM63040927-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.9	10.4
10°-20°	785.5	29.8
20°-30°	873.7	33.2
30°-40°	545.8	20.7
40°-50°	129.7	4.9
50°-60°	18.5	0.7
60°-70°	3.8	0.1
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1933.1	73.4
0°-40°	2478.9	94.2
0°-60°	2627.2	99.8
0°-90°	2632.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2632.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2868	
5°	2863	274
15°	2842	785
25°	1915	874
35°	899	546
45°	140	130
55°	14	19
65°	3	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582202

CATALOG NUMBER: HC630D010-HM63040927-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2868.0
2.5°	2855.9
5°	2862.8
7.5°	2873.1
10°	2876.5
12.5°	2874.9
15°	2841.9
17.5°	2731.4
20°	2527.3
22.5°	2240.4
25°	1915.4
27.5°	1604.2
30°	1339.8
32.5°	1120.2
35°	898.9
37.5°	660.4
40°	397.6
42.5°	230.0
45°	140.1
47.5°	89.9
50°	57.1
52.5°	32.8
55°	13.8
57.5°	6.9
60°	5.2
62.5°	5.2
65°	3.4
67.5°	3.4
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)