

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582936

Luminaire Tested: **HC6R05D010-HM60525927-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R05D010-HM60525927-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 590.7 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582936

CATALOG NUMBER: HC6R05D010-HM60525927-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582936

CATALOG NUMBER: HC6R05D010-HM60525927-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	80	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27405
5°	27999
10°	29681
15°	33184
20°	34741
25°	28967
30°	20269
35°	13652
40°	7027
45°	2442
50°	1092
55°	354
60°	164
65°	143
70°	128
75°	64
80°	95
85°	0



TEST NUMBER: P582936

CATALOG NUMBER: HC6R05D010-HM60525927-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	8.3
10°-20°	164.7	27.9
20°-30°	214.1	36.2
30°-40°	126.4	21.4
40°-50°	30.2	5.1
50°-60°	4.4	0.8
60°-70°	1.1	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.1	72.5
0°-40°	554.6	93.9
0°-60°	589.2	99.7
0°-90°	590.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	590.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	500	
5°	509	49
15°	585	165
25°	479	214
35°	204	126
45°	32	30
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P582936

CATALOG NUMBER: HC6R05D010-HM60525927-62RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	499.9
2.5°	501.0
5°	508.8
7.5°	519.0
10°	533.2
12.5°	555.7
15°	584.7
17.5°	604.1
20°	595.5
22.5°	552.0
25°	478.9
27.5°	395.3
30°	320.2
32.5°	259.1
35°	204.0
37.5°	150.0
40°	98.2
42.5°	53.7
45°	31.5
47.5°	19.5
50°	12.8
52.5°	7.5
55°	3.7
57.5°	1.9
60°	1.5
62.5°	1.5
65°	1.1
67.5°	0.8
70°	0.8
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)