

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593219

Luminaire Tested: **HC6R30D010-HM63040950-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R30D010-HM63040950-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3291.1 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593219

CATALOG NUMBER: HC6R30D010-HM63040950-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P593219

CATALOG NUMBER: HC6R30D010-HM63040950-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152652
5°	155992
10°	165355
15°	184831
20°	193526
25°	161356
30°	112929
35°	76051
40°	39166
45°	13606
50°	6055
55°	1998
60°	910
65°	817
70°	673
75°	445
80°	663
85°	0



TEST NUMBER: P593219

CATALOG NUMBER: HC6R30D010-HM63040950-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.8	8.3
10°-20°	917.6	27.9
20°-30°	1192.5	36.2
30°-40°	704.4	21.4
40°-50°	168.1	5.1
50°-60°	24.7	0.8
60°-70°	6.2	0.2
70°-80°	2.5	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2384.9	72.5
0°-40°	3089.3	93.9
0°-60°	3282.1	99.7
0°-90°	3291.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3291.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2785	
5°	2835	275
15°	3257	918
25°	2668	1193
35°	1136	704
45°	176	168
55°	21	25
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P593219

CATALOG NUMBER: HC6R30D010-HM63040950-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2784.6
2.5°	2790.8
5°	2834.7
7.5°	2891.2
10°	2970.5
12.5°	3095.9
15°	3256.7
17.5°	3365.3
20°	3317.3
22.5°	3075.0
25°	2667.6
27.5°	2201.8
30°	1784.0
32.5°	1443.4
35°	1136.4
37.5°	835.6
40°	547.3
42.5°	298.7
45°	175.5
47.5°	108.7
50°	71.0
52.5°	41.7
55°	20.9
57.5°	10.5
60°	8.3
62.5°	8.3
65°	6.3
67.5°	4.2
70°	4.2
72.5°	2.1
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)