

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582295

Luminaire Tested: **HC635D010-HM63040830-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040830-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3695.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582295

CATALOG NUMBER: HC635D010-HM63040830-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582295

CATALOG NUMBER: HC635D010-HM63040830-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132062
5°	131708
10°	129740
15°	127691
20°	123485
25°	117618
30°	107396
35°	86465
40°	58273
45°	42493
50°	36724
55°	33184
60°	31478
65°	29796
70°	28018
75°	26540
80°	24719
85°	22958



TEST NUMBER: P582295

CATALOG NUMBER: HC635D010-HM63040830-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.5	6.1
10°-20°	631.8	17.1
20°-30°	887.7	24.0
30°-40°	790.2	21.4
40°-50°	441.6	12.0
50°-60°	314.6	8.5
60°-70°	228.9	6.2
70°-80°	132.5	3.6
80°-90°	41.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.0	47.3
0°-40°	2536.2	68.6
0°-60°	3292.4	89.1
0°-90°	3695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2409	
5°	2393	227
15°	2250	632
25°	1944	888
35°	1292	790
45°	548	442
55°	347	315
65°	230	229
75°	125	133
85°	36	41
90°	0	



TEST NUMBER: P582295

CATALOG NUMBER: HC635D010-HM63040830-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2409.0
2.5°	2398.7
5°	2393.4
7.5°	2372.5
10°	2330.7
12.5°	2291.6
15°	2249.9
17.5°	2192.4
20°	2116.7
22.5°	2033.3
25°	1944.5
27.5°	1834.9
30°	1696.6
32.5°	1519.1
35°	1292.0
37.5°	1036.2
40°	814.3
42.5°	649.9
45°	548.1
47.5°	480.2
50°	430.6
52.5°	386.3
55°	347.2
57.5°	315.8
60°	287.1
62.5°	261.1
65°	229.7
67.5°	203.6
70°	174.8
72.5°	148.8
75°	125.3
77.5°	101.8
80°	78.3
82.5°	57.4
85°	36.5
87.5°	18.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)