

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582948

Luminaire Tested: **HC605D010-HM60525930-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC605D010-HM60525930-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 605.2 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582948

CATALOG NUMBER: HC605D010-HM60525930-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582948

CATALOG NUMBER: HC605D010-HM60525930-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 2 | 106 | 101 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 92 | 90 | 93 | 90 | 88 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 83 | 80 | 84 | 81 | 78 | 77 | 77 | 77 | 77 |
| 4 | 94 | 86 | 79 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 73 | 78 | 75 | 72 | 70 | 70 | 70 | 70 |
| 5 | 89 | 79 | 73 | 68 | 87 | 78 | 72 | 68 | 76 | 71 | 67 | 75 | 70 | 66 | 73 | 69 | 66 | 64 | 64 | 64 | 64 |
| 6 | 83 | 73 | 67 | 62 | 82 | 73 | 66 | 62 | 71 | 65 | 61 | 70 | 65 | 61 | 68 | 64 | 60 | 59 | 59 | 59 | 59 |
| 7 | 79 | 68 | 62 | 57 | 77 | 68 | 61 | 57 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 56 | 54 | 54 | 54 | 54 |
| 8 | 74 | 64 | 57 | 52 | 73 | 63 | 57 | 52 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 51 | 50 | 50 | 50 | 50 |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 46 | 46 | 46 | 46 |
| 10 | 66 | 56 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 53 | 48 | 44 | 43 | 43 | 43 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 23710 |
| 5° | 23861 |
| 10° | 24137 |
| 15° | 24631 |
| 20° | 24776 |
| 25° | 23995 |
| 30° | 21776 |
| 35° | 17701 |
| 40° | 11751 |
| 45° | 6536 |
| 50° | 3659 |
| 55° | 2026 |
| 60° | 1129 |
| 65° | 856 |
| 70° | 593 |
| 75° | 424 |
| 80° | 253 |
| 85° | 314 |



TEST NUMBER: P582948

CATALOG NUMBER: HC605D010-HM60525930-61WDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 41.4 | 6.8 |
| 10°-20° | 122.4 | 20.2 |
| 20°-30° | 180.4 | 29.8 |
| 30°-40° | 161.3 | 26.7 |
| 40°-50° | 70.0 | 11.6 |
| 50°-60° | 20.6 | 3.4 |
| 60°-70° | 6.6 | 1.1 |
| 70°-80° | 2.3 | 0.4 |
| 80°-90° | 0.4 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 344.2 | 56.9 |
| 0°-40° | 505.5 | 83.5 |
| 0°-60° | 596.0 | 98.5 |
| 0°-90° | 605.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 605.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 432 | |
| 5° | 434 | 41 |
| 15° | 434 | 122 |
| 25° | 397 | 180 |
| 35° | 264 | 161 |
| 45° | 84 | 70 |
| 55° | 21 | 21 |
| 65° | 7 | 7 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P582948

CATALOG NUMBER: HC605D010-HM60525930-61WDH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 432.5 |
| 2.5° | 431.2 |
| 5° | 433.6 |
| 7.5° | 434.5 |
| 10° | 433.6 |
| 12.5° | 433.6 |
| 15° | 434.0 |
| 17.5° | 431.5 |
| 20° | 424.7 |
| 22.5° | 412.8 |
| 25° | 396.7 |
| 27.5° | 374.3 |
| 30° | 344.0 |
| 32.5° | 307.9 |
| 35° | 264.5 |
| 37.5° | 214.9 |
| 40° | 164.2 |
| 42.5° | 120.0 |
| 45° | 84.3 |
| 47.5° | 60.2 |
| 50° | 42.9 |
| 52.5° | 30.7 |
| 55° | 21.2 |
| 57.5° | 14.4 |
| 60° | 10.3 |
| 62.5° | 8.1 |
| 65° | 6.6 |
| 67.5° | 4.9 |
| 70° | 3.7 |
| 72.5° | 2.8 |
| 75° | 2.0 |
| 77.5° | 1.6 |
| 80° | 0.8 |
| 82.5° | 0.5 |
| 85° | 0.5 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)