

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582336

Luminaire Tested: **HC635D010-HM63040840-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040840-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4208.2 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582336

CATALOG NUMBER: HC635D010-HM63040840-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582336

CATALOG NUMBER: HC635D010-HM63040840-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164806
5°	165903
10°	167821
15°	171261
20°	172227
25°	166860
30°	151378
35°	123078
40°	81696
45°	45462
50°	25492
55°	14155
60°	7806
65°	5902
70°	4119
75°	3008
80°	1799
85°	1761



TEST NUMBER: P582336

CATALOG NUMBER: HC635D010-HM63040840-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.8	6.8
10°-20°	850.9	20.2
20°-30°	1254.1	29.8
30°-40°	1121.7	26.7
40°-50°	486.6	11.6
50°-60°	143.0	3.4
60°-70°	45.6	1.1
70°-80°	16.1	0.4
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2392.7	56.9
0°-40°	3514.5	83.5
0°-60°	4144.1	98.5
0°-90°	4208.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4208.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3006	
5°	3015	288
15°	3018	851
25°	2759	1254
35°	1839	1122
45°	586	487
55°	148	143
65°	46	46
75°	14	16
85°	3	2
90°	0	



TEST NUMBER: P582336

CATALOG NUMBER: HC635D010-HM63040840-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3006.3
2.5°	2997.8
5°	3014.8
7.5°	3020.5
10°	3014.8
12.5°	3014.8
15°	3017.6
17.5°	3000.6
20°	2952.2
22.5°	2869.7
25°	2758.6
27.5°	2602.1
30°	2391.4
32.5°	2140.9
35°	1839.1
37.5°	1494.6
40°	1141.6
42.5°	834.2
45°	586.4
47.5°	418.5
50°	298.9
52.5°	213.6
55°	148.1
57.5°	99.7
60°	71.2
62.5°	56.9
65°	45.5
67.5°	34.2
70°	25.7
72.5°	20.0
75°	14.2
77.5°	11.4
80°	5.7
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)