

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593376

Luminaire Tested: **HC655D010-HM64560850-61WDBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC655D010-HM64560850-61WDBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5246.1 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593376

CATALOG NUMBER: HC655D010-HM64560850-61WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P593376

CATALOG NUMBER: HC655D010-HM64560850-61WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	95	92	96	93	90	93	91	88	90	88	86	85	85	85	85
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	95	86	80	75	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65	65	65	65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186312
5°	187678
10°	190951
15°	198526
20°	206850
25°	214228
30°	211362
35°	176108
40°	112933
45°	56393
50°	22379
55°	7598
60°	2182
65°	1544
70°	1266
75°	1673
80°	1263
85°	0



TEST NUMBER: P593376

CATALOG NUMBER: HC655D010-HM64560850-61WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.1	6.2
10°-20°	992.1	18.9
20°-30°	1620.0	30.9
30°-40°	1588.0	30.3
40°-50°	608.9	11.6
50°-60°	89.3	1.7
60°-70°	13.2	0.3
70°-80°	6.8	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2938.2	56.0
0°-40°	4526.3	86.3
0°-60°	5224.5	99.6
0°-90°	5246.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5246.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3399	
5°	3410	326
15°	3498	992
25°	3542	1620
35°	2632	1588
45°	727	609
55°	80	89
65°	12	13
75°	8	7
85°	0	2
90°	0	



TEST NUMBER: P593376

CATALOG NUMBER: HC655D010-HM64560850-61WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3398.6
2.5°	3390.6
5°	3410.5
7.5°	3422.4
10°	3430.3
12.5°	3458.3
15°	3498.0
17.5°	3529.8
20°	3545.7
22.5°	3549.7
25°	3541.7
27.5°	3486.1
30°	3339.0
32.5°	3060.8
35°	2631.5
37.5°	2102.8
40°	1578.1
42.5°	1124.9
45°	727.4
47.5°	445.2
50°	262.4
52.5°	151.1
55°	79.5
57.5°	35.7
60°	19.9
62.5°	15.9
65°	11.9
67.5°	11.9
70°	7.9
72.5°	7.9
75°	7.9
77.5°	4.0
80°	4.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)