

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582365

Luminaire Tested: **HC635D010-HM63040930-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040930-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3562.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582365

CATALOG NUMBER: HC635D010-HM63040930-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P582365

CATALOG NUMBER: HC635D010-HM63040930-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218042
5°	217119
10°	211987
15°	201227
20°	179361
25°	151085
30°	120373
35°	85876
40°	46187
45°	19785
50°	8998
55°	3278
60°	1612
65°	1271
70°	1186
75°	530
80°	789
85°	0



TEST NUMBER: P582365

CATALOG NUMBER: HC635D010-HM63040930-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.5	10.5
10°-20°	982.8	27.6
20°-30°	1138.3	32.0
30°-40°	787.1	22.1
40°-50°	227.3	6.4
50°-60°	39.1	1.1
60°-70°	10.0	0.3
70°-80°	3.9	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2493.6	70.0
0°-40°	3280.7	92.1
0°-60°	3547.0	99.6
0°-90°	3562.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3562.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3977	
5°	3946	372
15°	3546	983
25°	2498	1138
35°	1283	787
45°	255	227
55°	34	39
65°	10	10
75°	2	4
85°	0	1
90°	0	



TEST NUMBER: P582365

CATALOG NUMBER: HC635D010-HM63040930-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3977.4
2.5°	3960.2
5°	3945.5
7.5°	3901.4
10°	3808.2
12.5°	3695.2
15°	3545.6
17.5°	3334.6
20°	3074.5
22.5°	2787.4
25°	2497.8
27.5°	2201.0
30°	1901.6
32.5°	1602.3
35°	1283.2
37.5°	952.0
40°	645.4
42.5°	407.3
45°	255.2
47.5°	164.4
50°	105.5
52.5°	63.8
55°	34.3
57.5°	19.6
60°	14.7
62.5°	12.3
65°	9.8
67.5°	7.4
70°	7.4
72.5°	4.9
75°	2.5
77.5°	2.5
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)