

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582372

Luminaire Tested: **HC635D010-HM63040930-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582372  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC635D010-HM63040930-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3628.2 lumens  
Efficiency: N/A  
Efficacy: 107.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582372

CATALOG NUMBER: HC635D010-HM63040930-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582372

CATALOG NUMBER: HC635D010-HM63040930-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	142088
5°	143038
10°	144692
15°	147663
20°	148489
25°	143869
30°	130507
35°	106113
40°	70432
45°	39206
50°	21978
55°	12205
60°	6732
65°	5098
70°	3542
75°	2605
80°	1547
85°	1572



TEST NUMBER: P582372

CATALOG NUMBER: HC635D010-HM63040930-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	248.1	6.8
10°-20°	733.6	20.2
20°-30°	1081.3	29.8
30°-40°	967.1	26.7
40°-50°	419.6	11.6
50°-60°	123.3	3.4
60°-70°	39.3	1.1
70°-80°	13.9	0.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2063.0	56.9
0°-40°	3030.0	83.5
0°-60°	3572.9	98.5
0°-90°	3628.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3628.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2592	
5°	2599	248
15°	2602	734
25°	2378	1081
35°	1586	967
45°	506	420
55°	128	123
65°	39	39
75°	12	14
85°	2	2
90°	0	



TEST NUMBER: P582372

CATALOG NUMBER: HC635D010-HM63040930-61WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2591.9
2.5°	2584.6
5°	2599.3
7.5°	2604.3
10°	2599.3
12.5°	2599.3
15°	2601.8
17.5°	2587.0
20°	2545.3
22.5°	2474.2
25°	2378.5
27.5°	2243.4
30°	2061.7
32.5°	1845.7
35°	1585.6
37.5°	1288.6
40°	984.2
42.5°	719.2
45°	505.7
47.5°	360.8
50°	257.7
52.5°	184.0
55°	127.7
57.5°	85.9
60°	61.4
62.5°	49.1
65°	39.3
67.5°	29.4
70°	22.1
72.5°	17.2
75°	12.3
77.5°	9.8
80°	4.9
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)