

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582378

Luminaire Tested: **HC6R35D010-HM63040930-62RMDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC6R35D010-HM63040930-62RMDC  
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3866.1 lumens  
Efficiency: N/A  
Efficacy: 114.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582378

CATALOG NUMBER: HC6R35D010-HM63040930-62RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582378

CATALOG NUMBER: HC6R35D010-HM63040930-62RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	179322
5°	183248
10°	194252
15°	217130
20°	227333
25°	189549
30°	132660
35°	89336
40°	46008
45°	15978
50°	7113
55°	2342
60°	1074
65°	960
70°	785
75°	530
80°	789
85°	0



TEST NUMBER: P582378

CATALOG NUMBER: HC6R35D010-HM63040930-62RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	322.8	8.3
10°-20°	1077.9	27.9
20°-30°	1400.9	36.2
30°-40°	827.5	21.4
40°-50°	197.4	5.1
50°-60°	29.1	0.8
60°-70°	7.3	0.2
70°-80°	3.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2801.6	72.5
0°-40°	3629.1	93.9
0°-60°	3855.5	99.7
0°-90°	3866.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3866.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3271	
5°	3330	323
15°	3826	1078
25°	3134	1401
35°	1335	827
45°	206	197
55°	24	29
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P582378

CATALOG NUMBER: HC6R35D010-HM63040930-62RMDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3271.1
2.5°	3278.5
5°	3330.0
7.5°	3396.3
10°	3489.6
12.5°	3636.7
15°	3825.8
17.5°	3953.3
20°	3896.8
22.5°	3612.2
25°	3133.7
27.5°	2586.4
30°	2095.7
32.5°	1695.7
35°	1334.9
37.5°	981.6
40°	642.9
42.5°	350.9
45°	206.1
47.5°	127.6
50°	83.4
52.5°	49.1
55°	24.5
57.5°	12.3
60°	9.8
62.5°	9.8
65°	7.4
67.5°	4.9
70°	4.9
72.5°	2.5
75°	2.5
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)