

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583075

Luminaire Tested: **HC655D010-HM64560927-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC655D010-HM64560927-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4105.9 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583075

CATALOG NUMBER: HC655D010-HM64560927-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P583075

CATALOG NUMBER: HC655D010-HM64560927-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140120
5°	140028
10°	138680
15°	137243
20°	133362
25°	127731
30°	118544
35°	101997
40°	74447
45°	51013
50°	41005
55°	35736
60°	32980
65°	31365
70°	29300
75°	27387
80°	24877
85°	21197



TEST NUMBER: P583075

CATALOG NUMBER: HC655D010-HM64560927-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.2	5.9
10°-20°	679.1	16.5
20°-30°	965.9	23.5
30°-40°	929.9	22.6
40°-50°	535.0	13.0
50°-60°	339.0	8.3
60°-70°	240.0	5.8
70°-80°	136.8	3.3
80°-90°	39.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1886.3	45.9
0°-40°	2816.2	68.6
0°-60°	3690.2	89.9
0°-90°	4105.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4105.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2556	
5°	2545	241
15°	2418	679
25°	2112	966
35°	1524	930
45°	658	535
55°	374	339
65°	242	240
75°	129	137
85°	34	39
90°	0	



TEST NUMBER: P583075

CATALOG NUMBER: HC655D010-HM64560927-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2556.0
2.5°	2544.6
5°	2544.6
7.5°	2527.8
10°	2491.3
12.5°	2454.7
15°	2418.2
17.5°	2362.0
20°	2286.0
22.5°	2201.7
25°	2111.7
27.5°	2002.0
30°	1872.7
32.5°	1715.2
35°	1524.1
37.5°	1290.7
40°	1040.3
42.5°	821.0
45°	658.0
47.5°	553.9
50°	480.8
52.5°	421.7
55°	373.9
57.5°	331.8
60°	300.8
62.5°	272.8
65°	241.8
67.5°	213.6
70°	182.8
72.5°	154.6
75°	129.3
77.5°	104.0
80°	78.8
82.5°	56.2
85°	33.7
87.5°	14.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)