

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582367

Luminaire Tested: **HC635D010-HM63040930-61PSMDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC635D010-HM63040930-61PSMDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3473.6 lumens  
Efficiency: N/A  
Efficacy: 103.1 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582367

CATALOG NUMBER: HC635D010-HM63040930-61PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582367

CATALOG NUMBER: HC635D010-HM63040930-61PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124157
5°	123822
10°	121975
15°	120040
20°	116093
25°	110571
30°	100959
35°	81285
40°	54788
45°	39942
50°	34523
55°	31186
60°	29592
65°	28006
70°	26351
75°	24951
80°	23235
85°	21574



TEST NUMBER: P582367

CATALOG NUMBER: HC635D010-HM63040930-61PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.0	6.1
10°-20°	594.0	17.1
20°-30°	834.5	24.0
30°-40°	742.8	21.4
40°-50°	415.1	12.0
50°-60°	295.8	8.5
60°-70°	215.2	6.2
70°-80°	124.6	3.6
80°-90°	38.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1641.4	47.3
0°-40°	2384.3	68.6
0°-60°	3095.1	89.1
0°-90°	3473.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3473.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2265	
5°	2250	213
15°	2115	594
25°	1828	834
35°	1215	743
45°	515	415
55°	326	296
65°	216	215
75°	118	125
85°	34	39
90°	0	



TEST NUMBER: P582367

CATALOG NUMBER: HC635D010-HM63040930-61PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2264.8
2.5°	2255.0
5°	2250.1
7.5°	2230.4
10°	2191.2
12.5°	2154.4
15°	2115.1
17.5°	2061.2
20°	1990.0
22.5°	1911.4
25°	1828.0
27.5°	1724.9
30°	1594.9
32.5°	1428.1
35°	1214.6
37.5°	974.1
40°	765.6
42.5°	610.9
45°	515.2
47.5°	451.5
50°	404.8
52.5°	363.2
55°	326.3
57.5°	296.9
60°	269.9
62.5°	245.4
65°	215.9
67.5°	191.4
70°	164.4
72.5°	139.8
75°	117.8
77.5°	95.7
80°	73.6
82.5°	54.0
85°	34.3
87.5°	17.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)