

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582505

Luminaire Tested: **HC640D010-HM63040930-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582505  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC640D010-HM63040930-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4492.2 lumens  
Efficiency: N/A  
Efficacy: 109.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582505

CATALOG NUMBER: HC640D010-HM63040930-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582505

CATALOG NUMBER: HC640D010-HM63040930-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	213322
5°	216651
10°	228987
15°	254962
20°	264407
25°	216938
30°	152017
35°	103711
40°	54023
45°	18986
50°	8503
55°	2724
60°	1557
65°	1116
70°	914
75°	614
80°	0
85°	0



TEST NUMBER: P582505

CATALOG NUMBER: HC640D010-HM63040930-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	381.4	8.5
10°-20°	1263.4	28.1
20°-30°	1608.7	35.8
30°-40°	958.8	21.3
40°-50°	232.5	5.2
50°-60°	35.7	0.8
60°-70°	8.8	0.2
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3253.5	72.4
0°-40°	4212.3	93.8
0°-60°	4480.4	99.7
0°-90°	4492.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4492.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3891	
5°	3937	381
15°	4492	1263
25°	3586	1609
35°	1550	959
45°	245	232
55°	28	36
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582505

CATALOG NUMBER: HC640D010-HM63040930-61MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3891.3
2.5°	3891.3
5°	3937.0
7.5°	4008.2
10°	4113.6
12.5°	4278.8
15°	4492.4
17.5°	4626.4
20°	4532.3
22.5°	4170.5
25°	3586.5
27.5°	2942.7
30°	2401.5
32.5°	1962.8
35°	1549.7
37.5°	1142.4
40°	754.9
42.5°	407.3
45°	244.9
47.5°	153.8
50°	99.7
52.5°	59.9
55°	28.5
57.5°	17.1
60°	14.2
62.5°	11.3
65°	8.6
67.5°	5.7
70°	5.7
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)