

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583153

Luminaire Tested: **HC660D010-HM64560830-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560830-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6005.4 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583153

CATALOG NUMBER: HC660D010-HM64560830-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P583153

CATALOG NUMBER: HC660D010-HM64560830-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285180
5°	289626
10°	306118
15°	340848
20°	353472
25°	290019
30°	203221
35°	138645
40°	72221
45°	25390
50°	11368
55°	3632
60°	2094
65°	1479
70°	1234
75°	805
80°	0
85°	0



TEST NUMBER: P583153

CATALOG NUMBER: HC660D010-HM64560830-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	509.8	8.5
10°-20°	1689.0	28.1
20°-30°	2150.6	35.8
30°-40°	1281.7	21.3
40°-50°	310.8	5.2
50°-60°	47.7	0.8
60°-70°	11.8	0.2
70°-80°	4.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4349.4	72.4
0°-40°	5631.2	93.8
0°-60°	5989.6	99.7
0°-90°	6005.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6005.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5202	
5°	5263	510
15°	6006	1689
25°	4795	2151
35°	2072	1282
45°	328	311
55°	38	48
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P583153

CATALOG NUMBER: HC660D010-HM64560830-61MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5202.1
2.5°	5202.1
5°	5263.1
7.5°	5358.2
10°	5499.2
12.5°	5720.0
15°	6005.7
17.5°	6184.7
20°	6059.0
22.5°	5575.4
25°	4794.7
27.5°	3934.0
30°	3210.4
32.5°	2623.9
35°	2071.7
37.5°	1527.1
40°	1009.2
42.5°	544.6
45°	327.5
47.5°	205.6
50°	133.3
52.5°	80.0
55°	38.0
57.5°	22.8
60°	19.1
62.5°	15.2
65°	11.4
67.5°	7.7
70°	7.7
72.5°	3.8
75°	3.8
77.5°	3.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)