

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582547

Luminaire Tested: **HC640D010-HM63040940-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC640D010-HM63040940-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4079.7 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582547

CATALOG NUMBER: HC640D010-HM63040940-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582547

CATALOG NUMBER: HC640D010-HM63040940-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145816
5°	145421
10°	143256
15°	140983
20°	136343
25°	129860
30°	118569
35°	95466
40°	64349
45°	46920
50°	40553
55°	36634
60°	34756
65°	32896
70°	30951
75°	29314
80°	27276
85°	25411



TEST NUMBER: P582547

CATALOG NUMBER: HC640D010-HM63040940-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.1	6.1
10°-20°	697.6	17.1
20°-30°	980.1	24.0
30°-40°	872.4	21.4
40°-50°	487.5	12.0
50°-60°	347.4	8.5
60°-70°	252.7	6.2
70°-80°	146.3	3.6
80°-90°	45.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1927.8	47.3
0°-40°	2800.2	68.6
0°-60°	3635.2	89.1
0°-90°	4079.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4079.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2660	
5°	2643	250
15°	2484	698
25°	2147	980
35°	1426	872
45°	605	488
55°	383	347
65°	254	253
75°	138	146
85°	40	45
90°	0	



TEST NUMBER: P582547

CATALOG NUMBER: HC640D010-HM63040940-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2659.9
2.5°	2648.4
5°	2642.6
7.5°	2619.5
10°	2573.5
12.5°	2530.2
15°	2484.1
17.5°	2420.8
20°	2337.1
22.5°	2244.9
25°	2146.9
27.5°	2025.9
30°	1873.1
32.5°	1677.2
35°	1426.5
37.5°	1144.1
40°	899.2
42.5°	717.5
45°	605.2
47.5°	530.2
50°	475.5
52.5°	426.6
55°	383.3
57.5°	348.7
60°	317.0
62.5°	288.2
65°	253.6
67.5°	224.8
70°	193.1
72.5°	164.2
75°	138.4
77.5°	112.4
80°	86.4
82.5°	63.4
85°	40.4
87.5°	20.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)